





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



| | |
|----------------------------|------------------------------------|
| ANGLE TOLERANCE (°) | ±8 |
| DIFFUSING ANGLE (°) | 80 (FWHM) |
| DAMAGE THRESHOLD, PULSED | 0.22 J/cm² @ 1064nm @ 10ns |
| OPERATING TEMPERATURE (°C) | -30 to +100 (Maximum of 240 Hours) |
| SUBSTRATE | Polycarbonate |
| TRANSMISSION (%) | >85 |
| WAVELENGTH RANGE (nm) | 400 - 700 |
| RoHS | COMPLIANT |

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

| | | | | |
|---|--------|--------------------------------------|-----------------|--|
| THIRD ANGLE PROJECTION  | TITLE | 80° Diffusing Angle 50mm Dia Mounted | | |
| | DWG NO | 54507 | SHEET 1 OF 1 | |