


NOTES:

1. COATING (APPLY ACROSS CLEAR APERTURE)
LASER V-COAT
 $R(ABS) \leq 0.25\% @ 1064nm$
2. ROHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

DAMAGE THRESHOLD, (PULSED)	15 J/cm ² @ 20ns, 20Hz, 1064nm
DESIGN WAVELENGTH DWL (nm)	1064nm
EXPANSION POWER	20X
TRANSMISSION %	>98.5 (nominal)
TRANSMITTED WAVEFRONT, P-V	< $\lambda/10$ for 1.1mm input beam (nominal)



ALL DIMS IN

mm

EO® Edmund Optics®

TITLE

20X, 1064nm Vega Laser Line Beam Expander

DWG NO

35121

SHEET
1 OF 1