

NOTES:




1. SUBSTRATE MATERIAL:  
CALCIUM FLUORIDE (CAF2)
2. COATING (APPLY ACROSS CLEAR APERTURE)

S1:  
50/50 ± 20% @ 800 - 2500nm  
25/75 ± 15% @ 2500 - 600nm

S2:  
NONE

3. RoHS COMPLIANT


4.  GROUND SURFACE



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	60-40	60-40
SURFACE FLATNESS	3λ/4	3λ/4
CLEAR APERTURE	Ø45.00	Ø45.00

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics®**

TITLE	25mm Diameter, 0.8-6µm Calcium Fluoride IR Plate Beamsplitter	
DWG NO	36657	SHEET 1 OF 1