





NOTES:

1. SUBSTRATE MATERIAL:
FUSED SILICA
2. CENTERING TOLERANCE (AT 587.6nm):
PLANO AXIS WEDGE: < 5 ARCMIN
POWER ASIX WEDGE: < 5 ARCMIN
AXIAL TWIST: < 3 ARCMIN
3. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2:
 $R(AVG) \leq 1.5\%$ FROM 250-700nm @ 0° AOI
 $R(ABS) \leq 1.0\%$ FROM 350-450nm @ 0° AOI
4.  FINE GROUND SURFACE
5. POWER, IRREGULARITY, AND SURFACE QUALITY
SPECIFICAIONS APPLY ACROSS CLEAR APERTURE
6. ROHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

	S1	S2				
SHAPE	CONVEX	PLANO				
SURFACE QUALITY	40 - 20	40 - 20				
CLEAR APERTURE	11.43 x 11.43	11.43 x 11.43				
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED				

	TITLE		LENS CYL SHAPING 12.7mm SQ x 50mm UV VIS	
	DWG NO	36107	SHEET 1 OF 1	

ALL DIMS IN	mm		
-------------	----	--	--