



NOTES:

1. SUBSTRATE:  
D-ZK3
2. NUMERICAL APERTURE: 0.24
3. COATING  
S1 & S2: R(ABS) < 1.0% @ 600 - 1050nm
4. FOCAL LENGTH TOLERANCE: ±1%
5. TRANSMITTED WAVEFRONT ERROR ( $\lambda$ , RMS): < 0.087



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	11.00	 <b>Edmund Optics®</b>	
			BFL	9.30		
SHAPE	CONVEX	PLANO	THIRD ANGLE PROJECTION		TITLE	0.24 NA 11.00mm FL 600-1050nm AR Coated, Molded Aspheric Lens
SURFACE QUALITY	80-50	80-50	ALL DIMS IN	mm	DWG NO	37110
CLEAR APERTURE	Ø5.40	Ø5.40				SHEET 1 OF 1
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				