

NOTES:


1. SUBSTRATE:
Fused Silica
2. S2 TO BE PARALLEL TO S1 TO WITHIN <3 ARCMINS
3. COATING (APPLY ACROSS COATING APERTURE)

S1 & S2: 266nm High Laser AR Coating
R(ABS) < 0.10% @ 266nm @ 0° AOI

DAMAGE THRESHOLD,
PUSLED: 3 J/cm² @ 20ns , 20 Hz @ 266nm


4. FINE GROUND SURFACE

5. CLEAR APERTURE AND COATING APERTURE ARE CENTERED ON SURFACE
6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2				
SHAPE	PLANO	PLANO				
SURFACE QUALITY	10-5	10-5				
SURFACE FLATNESS	0.10 WAVE	0.10 WAVE	TITLE			
CLEAR APERTURE	Ø17.19	Ø17.19				
COATING APERTURE	Ø17.19	Ø17.19	0.1R 266nm Laser Window 19.1 Dia x 6.35			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				
			ALL DIMS IN	mm	DWG NO	11221
						SHEET 1 OF 1

 **Edmund Optics®**

0.1R 266nm Laser Window 19.1 Dia x 6.35