




NOTES:

1. EXIT BEAMS 1 & 2 PARALLEL AFTER BONDING TO <30 arcsec
3. COATING (APPLY ACROSS CLEAR APERTURE)
 - S1: R(avg) <0.5% @ 430 - 670nm
 - S2: AVERAGE TRANSMITTANCE 45% ±5% @ 430 - 670nm AT 45° AOI
 - ABSORPTION <10% @ 430 - 670nm @ 45° AOI
 - POLARIZATION DEVIATION <6% @ 430 - 670nm @ 45° AOI
 - S3: NONE
4. RoHS COMPLIANT



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



REV. A	S1	S2	THIRD ANGLE PROJECTION		TITLE	20mm, VIS, LATERAL DISPLACEMENT NON-POLARIZED BEAMSPLITTER	
SURFACE QUALITY	40-20	40-20	ALL DIMS IN	mm	DWG NO	47189	SHEET 1 OF 1
SURFACE FLATNESS	$\lambda/8$	$\lambda/8$					