




NOTES:

1. EXIT BEAMS 1 & 2 PARALLEL AFTER BONDING TO < 2 ARCMIN
3. COATING (APPLY ACROSS CLEAR APERTURE)
  - S1: R(avg) < 0.5% @ 720 - 1080nm
  - S2: AVERAGE TRANSMITTANCE 45% ±5% @ 720 - 1080nm AT 45° AOI  
 ABSORPTION < 10% @ 720 - 1080nm @ 45° AOI  
 POLARIZATION DEVIATION < 6% @ 720 - 1080nm @ 45° AOI
  - S3: NONE
4. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY



REV. A	S1	S2	THIRD ANGLE PROJECTION		TITLE	10mm, NIR, LATERAL DISPLACEMENT NON-POLARIZED BEAMSPLITTER	
SURFACE QUALITY	40-20	40-20	ALL DIMS IN	mm	DWG NO	47540	SHEET 1 OF 1
SURFACE FLATNESS	$\lambda/8$	$\lambda/8$					