


NOTES:

1. SUBSTRATE:
FLOAT GLASS
2. COATING METHOD: SPUTTERED CHROME
3. OPTICAL DENSITY: 2.8+
4. FREQUENCY (lp/mm): 0.31 - 7.14
5. LINE WIDTH: 1.6 - 0.070
6. NUMBER OF SECTORS: 60
7. PATTERN DIAMETER: 62.5mm
8. WEDGE ANGLE: 6°
9. SURFACE QUALITY: 60-40



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	STAR TARGET CHROME ON GLASS	
ALL DIMS IN	mm	DWG NO	46247	SHEET 1 OF 1