




NOTES:


1. LASER CLASS:  
IIIb
2. BEAM DIAMETER(mm): 3.5 Typical  
BEAM DIVERGENCE: <0.5 mrad
3. MODULATION FREQUENCY: 0 - 10 kHz
4. OPERATING TEMPERATURE: 15 to 30 °C  
OPERATING VOLTAGE: 5V
5. OUTPUT POWER: 10mW
6. WAVELENGTH RANGE: 405±5 nm



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**EO**® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	10mW, 405nm Violet Alignment Laser Diode Module	
ALL DIMS IN	mm	DWG NO	37025	SHEET 1 OF 1