



- NOTES:
- 1. SUBSTRATE: IR GRADE FUSED SILICA
 - 2. COATING:
S1 & S2: R(ABS) <0.1% @ 1900 - 2200nm
 - 3. CENTERING: < 3 ARCMIN
 - 4. RoHS: COMPLIANT


**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	CONVEX	PLANO
SURFACE QUALITY	20-10	20-10
CLEAR APERTURE	Ø22.86	Ø22.86
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

EFL: 350.41 mm		 Edmund Optics®		
BFL: 349.31 mm				
THIRD ANGLE PROJECTION 		TITLE	25.4mm Diameter x 350mm FL, 1900-2200nm Coated, IR Ultrafast Thin PCX Lens	
ALL DIMS IN	mm	DWG NO	11625	SHEET 1 OF 1