




FOCAL LENGTH (EFL): $4,5 \pm 0,05$

BACK FOCAL LENGTH (BFL): 3,78

1 AR COATING:

$\frac{1}{4}$ WAVE MgF2 @ 550nm
 $R(\text{AVG}) < 1,75\%$ FROM 400-700nm (N-BK7)

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$4,29 \pm 0,004$ CX	GLASS N-BK7 517/642	R	$4,29 \pm 0,004$ CX
Øe	2,5		Øe	2,5
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	87,04'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED


ROHS: COMPLIANT
 SCALE: NONE $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

3mm Dia, x 4,5mm FL, MgF2 Coated, Double-Convex Lens

DWG NO

31859

SHEET SIZE
A4

SHEET
1 OF 1