





FOCAL LENGTH (EFL): 150 ± 1,5
BACK FOCAL LENGTH (BFL): 147,82

1 AR COATING: NONE

LEFT SURFACE			MATERIAL	RIGHT SURFACE		
R	68,789±0,069 CX		GLASS FUSED SILICA 458/678	R	∞ PL	
Øe	24			Øe	24	
3/	0,5 (0,1) λ=632,8 nm			3/	0,5 (0,1) λ=632,8 nm	
4/	-			4/	2,18'	
5/	20 - 10 (MIL-PRF-13830B)			5/	20 - 10 (MIL-PRF-13830B)	
6/	-			6/	-	
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION	 Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY				TITLE	25mm Dia, x 150mm FL Uncoated, λ/20 PCX Lens	
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING				ALL DIMS IN:	mm	
INDICATIONS IN ACCORDANCE WITH ISO 10110			DWG NO	33054	SHEET SIZE A4	SHEET 1 OF 1