



NOTES:

- 1. SUBSTRATE: FUSED SILICA
- 2. COATING (APPLY ACROSS CLEAR APERTURE)
  - S1: NONE
  - S2: 1064nm Laser AR Coating
  - R(ABS) < 0.25% @ 1064nm @ 0° AOI
- DAMAGE THRESHOLD
  - PULSED: 15J/cm² @ 20ns, 20Hz @ 1064nm

3 FINE GRIND SURFACE

- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20-10	20-10
CLEAR APERTURE	31.81 x 22.50	Ø22.50
SURFACE FLATNESS	λ/20	λ/20
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION

ALL DIMS IN	mm	TITLE	25mm 1/20 WV 1064nm AR CTD HT RA FS PRISM	
		DWG NO	37639	SHEET 1 OF 1