




FOCAL LENGTH (EFL): 54 ±0,54
BACK FOCAL LENGTH (BFL): 51,6

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	24,755±0,025 CX	GLASS FUSED SILICA 458/678	R	∞ PL
Øe	17		Øe	17
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	2,18'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT SCALE: NONE λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE 18mm Dia x 54mm FL, Uncoated, UV Plano-Convex Lens

DWG NO 36688

SHEET SIZE A4

SHEET 1 OF 1