

NOTES:


1. SUBSTRATE
FUSED SILICA
2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN <3 ARCMIN
3. COATING (APPLY ACROSS COATING APERTURE):

S1: 266 HR Coating
R (ABS) > 99.5% @ 266nm @ 45° AOI
R (AVG) > 99.5% @ 263 - 268nm @ 45° AOI

DAMAGE THRESHOLD,
PULSED: 2.5 J/cm², 20ns, 20Hz @ 266nm
CW: 1MW/cm² @ 266nm

S2: NONE



4. FINE GRIND SURFACE
5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY
ACROSS CLEAR APERTURE
6. CLEAR APERTURE AND COATING APERTURE ARE CENTERED ON SURFACES
7. APPLY ARROW ON EDGE WITH LASER ETCH, PENCIL, OR PERMANENT INK
POINTING TOWARDS SURFACE S1



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	10-5	COMMERCIAL POLISH
SURFACE FLATNESS	0.10 WAVE	N/A
MIN CLEAR APERTURE	Ø5.40	N/A
MIN COATING APERTURE	Ø5.72	N/A
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	Ø6.35mm x 4mm, 266nm, NdYAG MIRROR 45° AOI
ALL DIMS IN	mm	DWG NO	38829
			SHEET 1 OF 1