



NOTES:


1. SUBSTRATE
Corning Eagle XG
2. COATING (APPLY ACROSS COATING APERTURE)
S1: NONE
S2: R(ABS) <2.0% @ 420 - 670nm@ 45 ± 15° AOI
3. WAVELENGTH RANGE: 420 - 670
4. OPERATING TEMPERATURE: -40 to +200 °C
5. THERMAL EXPANSION: 31.7 x 10⁻⁷/°C
6. CONSTRUCTION: Wire Grid
7. ROHS: COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION 		TITLE	12.5mm Square Broadband Polarizing Plate Beamsplitter	
SHAPE	PLANO	PLANO	ALL DIMS IN	mm	DWG NO	48544	SHEET 1 OF 1
SURFACE QUALITY	80-50	80-50					
CLEAR APERTURE	8.5 x 8.5	8.5 x 8.5					