



NOTES:

1. SUBSTRATE
FUSED SILICA WITH CHROME DEPOSIT
2. OPTICAL DENSITY:
>7 @ 400nm
6 @ 550nm
4.5 @ 750nm
3.6 @ 1000nm
3. SPECTRAL RANGE: 200 - 2000nm
4. PATTERN: 1 CENTRAL SIEMENS STAR WITH 36 SEGMENT PAIRS, 8mm DIAMETER
PATTERN TOLERANCE: 100nm/cm = 10⁻⁵
5. CONSTRUCTION: STAINLESS STEEL, 75 x 25 x 1.5mm, MICROSCOPE SLIDE
FORMAT
6. ROHS: COMPLIANT




DETAIL A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION 		TITLE		
ALL DIMS IN	mm	DWG NO	37538	SHEET 1 OF 1