

## NOTES:

- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL TO S1 TO WITHIN <1 ARCMIN
- COATING (APPLY ACROSS COATING APERTURE)
  \$1 & \$2: MgF2 (400-700nm)
  R(AVG) ≤ 1.75% @ 400 700nm



5. ROHS COMPLIANT





PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

			-	
	\$1	\$2		
SHAPE	PLANO	PLANO		1
SURFACE QUALITY	60-40	60-40	THIRD ANGLE . PROJECTION	$\oplus \lhd$
WAVELENGTH RANGE	400 - 700nm	400 - 700nm		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm

				Edmund Optic	;S®	
	THIRD ANGLE _ PROJECTION		TITLE	100mm DIA., 6mm THICK, MgF2 COATE N-BK7 WINDOW	nm DIA., 6mm THICK, MgF2 COATED λ/4 N-BK7 WINDOW	
_	ALL DIMS IN	mm	DWG NO	11859	SHEET 1 OF 1	

R



1 OF 1