




NOTES:

- MATERIAL: II-VI OPTICAL GRADE POLYCRYSTALLINE CVD DIAMOND
 BULK ABSORPTION @ 10.6µm: <0.07cm-1
 BULK ABSORPTION @ 1µm: <1cm-1
 SCATTER @ 1µm: <0.7cm-1
 INDEX OF REFRACTION: 2.38 @ 10.6µm
- SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN <5 ARCMIN
- COATING (APPLY ACROSS CLEAR APERTURE):
 S1 & S2: NONE
- RoHS: COMPLIANT



**FOR INFORMATION ONLY:
 DO NOT MANUFACTURE
 PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
MIN CLEAR APERTURE	9.00 x 9.00	9.00 x 9.00
BEVEL MAX FACE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED



ALL DIMS IN mm

EO® Edmund Optics®

TITLE

10mm Square, 0.7mm Thick, Uncoated Polycrystalline CVD Diamond Window

DWG NO

12668

SHEET 1 OF 1