




FOCAL LENGTH (EFL): $3 \pm 0,03$
 BACK FOCAL LENGTH (BFL): 2,57

1 AR COATING: NIR I
 $R(\text{AVG}) \leq 0,5\%$ FROM 600-1050nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	2,55±0,003 CX	GLASS N-LaSF9 850/322	R	∞ PL
Øe	2		Øe	2
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	52,94'
5/	20 - 10 (MIL-PRF-13830B)		5/	20 - 10 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT SCALE: NONE λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

2,5mm Dia, x 3,0mm FL, NIR I Coated, Plano-Convex Lens

DWG NO

45959

SHEET SIZE
A4

SHEET
1 OF 1