




FOCAL LENGTH (EFL): $10 \pm 0,1$
 BACK FOCAL LENGTH (BFL): 8,491

1 AR COATING: NONE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	7,85±0,008 CX	GLASS N-SF11 785/258	R	∞ PL
Øe	8,1		Øe	8,1
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	3,82'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-


PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

$\lambda = 587,6$ nm

FIRST ANGLE
PROJECTION



Edmund Optics®

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm

TITLE

9mm Dia x 10mm FL, Uncoated, Plano-
Convex Lens

DWG NO

37778

SHEET SIZE
A4

SHEET
1 OF 1