




FOCAL LENGTH (EFL): 42 ±0,42
 BACK FOCAL LENGTH (BFL): 40,22

- 1 AR COATING: NIR II
 $R(ABS) \leq 1,5\%$ FROM 750-800nm @ 0° AOI
 $R(ABS) \leq 1,0\%$ FROM 800-1550nm @ 0° AOI
 $R(AVG) \leq 0,7\%$ FROM 750-1550nm @ 0° AOI
- 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	21,71±0,022 CX	GLASS N-BK7 517/642	R	∞ PL
Øe	11		Øe	11
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
 SCALE: NONE
 $\lambda = 587,6\text{nm}$

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

12,0mm Dia, x 42,0mm FL, NIR II, Inked, Plano-Convex Lens

DWG NO

67500INK

SHEET SIZE
A4

SHEET
1 OF 1