

LEFT SURFACE			MATERIAL		RIGHT SURFACE		
R	102,93±0,103 CX		GLASS	N-BK7 517/642	R	102,93±0,103 CX	
Øe	9				Øe	9	
3/	3 (0,5) λ=632,8 nm				3/	3 (0,5) λ=632,8 nm	
4/	-				4/	1,93'	
5/	40 - 20 (MIL-PRF-13830B)				5/	40 - 20 (MIL-PRF-13830B)	
6/	-				6/	-	
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION		Edmund Optics®		
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE 10mm Dia, x 100mm FL, Uncoated, Double-Convex Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING							
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm	DWG NO 63542	SHEET SIZE A4	SHEET 1 OF 1