




FOCAL LENGTH (EFL): 27 ±0,27
 BACK FOCAL LENGTH (BFL): 25,34

1 AR COATING: 633nm V-COAT
 R(ABS) < 0,25% @ 633nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	13,95±0,014 CX	GLASS N-BK7 517/642	R	∞ PL
Øe	8,1		Øe	8,1
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®							
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE		9,0mm Diameter x 27,0mm FL, 633nm V-Coat, PCX Lens					
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					ALL DIMS IN:		mm	DWG NO	65496		SHEET SIZE	SHEET 1 OF 1
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING									A4			
INDICATIONS IN ACCORDANCE WITH ISO 10110												