




FOCAL LENGTH (EFL): $18 \pm 0,18$
 BACK FOCAL LENGTH (BFL): 16,69

1 AR COATING: VIS-EXT
 $R(\text{AVG}) \leq 0,5\%$ FROM 350-700nm @ 0° AOI

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$27,22 \pm 0,027$ CX	GLASS N-SF11 785/258	R	$27,22 \pm 0,027$ CX
Øe	17		Øe	17
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,27'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
 SCALE: NONE $\lambda = 587,6$ nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

18mm Dia, x 18mm FL, VIS-EXT Coated, Double-Convex Lens

DWG NO

89165

SHEET SIZE
A4

SHEET
1 OF 1