




FOCAL LENGTH (EFL): 40 ±0,4
 BACK FOCAL LENGTH (BFL): 37,54

- 1 AR COATING: VIS-EXT
 R(AVG) ≤ 0,5% FROM 350-700nm @ 0° AOI
- 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	60,85±0,061 CX	GLASS N-SF11 785/258	R	60,85±0,061 CX
Øe	39		Øe	39
3/	3 (0,5) λ=632,8 nm		3/	3 (0,5) λ=632,8 nm
4/	-		4/	1,27'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS: COMPLIANT
 SCALE: NONE
 λ = 587,6nm

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

FIRST ANGLE PROJECTION



ALL DIMS IN: mm



Edmund Optics®

TITLE

40mm Dia, x 40mm FL, VIS-EXT
 Coated, Inked, Double-Convex Lens

DWG NO

89193INK

SHEET SIZE
 A4

SHEET
 1 OF 1