


- NOTES:
- 1. COATING (APPLY ACROSS CLEAR APERTURE)  
LASER V-COAT  
 $R(ABS) \leq 0.25\% @ 266nm$
  - 2. RoHS: COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

DAMAGE THRESHOLD (PULSED)	1.5J/cm² @ 10ns, 20Hz, 266nm
DESIGN WAVELENGTH DWL (nm)	266
EXPANSION POWER	1.5X
TRANSMISSION (%)	> 99 (NOMINAL)
NOMINAL PERFORMANCE	<λ/10 FOR 4mm INPUT BEAM (NOMINAL)



ALL DIMS IN mm

**Edmund Optics®**

TITLE  
1.5X, 266nm VEGA™ Nd:YAG LASER LINE  
BEAM EXPANDER

DWG NO 12872

SHEET  
1 OF 1