## **NOTES:**

1. SUBSTRATE: FUSED SILICA

2. BEAM MODE: SM OR MM

3. OVERALL EFFICIENCY: 92%


4. RING ANGLE: 1.35°


5. ZERO ORDER, RELATIVE TO THE INCIDENT BEAM: <1%

6. COATING: LASER V-COAT(1064nm)

7. BEAM SPECIFICATION:

MINIMUM BEAM DIAMETER: 0.27mm





## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

			Edmund Optics
\$1	\$2		10/4mm OF 4mm DIA DIFFDACTIVE AVICON

	\$1	S2		1		1044nm 25.4mm DIA DIEEPA	CTIVE AVICON
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION		TITLE	1064nm, 25.4mm DIA., DIFFRACTIVE AXICON	
MIN CLEAR APERTURE	Ø22.9mm	Ø22.9mm		1			CHEET
BEVEL MAX FACE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	14678	SHEET 1 OF 1