



NOTES:

1. SUBSTRATE: FUSED SILICA
2. BEAM MODE: SM TEM00, $M^2 < 1.5$
3. OVERALL EFFICIENCY: 95%
4. FULL ANGLE AT $1/e^2$ (mRad): 0.38
5. COATING:
LASER V-COAT (532nm)
6. BEAM SPECIFICATION:
MINIMUM BEAM DIAMETER: 5mm
OUTPUT SHAPE: SQUARE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

	S1	S2	THIRD ANGLE PROJECTION 		TITLE	532nm, 25.4mm DIA., TOP-HAT DIFFRACTIVE BEAM SHAPER	
SHAPE	PLANO	PLANO	ALL DIMS IN	mm	DWG NO	14680	SHEET 1 OF 1
MIN CLEAR APERTURE	Ø22.9	Ø22.9					
BEVEL MAX FACE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					