NOTES:

1. SUBSTRATE: FUSED SILICA

2. BEAM MODE: SM OR MM


3. SAMPLED ENERGY: 73


4. SAMPLED ANGLE: 2.0 x 2.0

5. COATING: LASER V-COAT (532nm)

6. BEAM SPECIFICATION:

MINIMUM BEAM DIAMETER: 0.37mm





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	Edmund	Optics®

	S1 S2				532nm, 20mm Dia., 9x9 SPOT MATRIX,		
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION	TITLE	DIFFRACTIVE BEAMSPLITTER		
MIN CLEAR APERTURE	Ø18	Ø18	'			CHEET	
BEVEL MAX FACE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED /	ALL DIMS IN m	mm	DWG NO	14688	SHEET 1 OF 1