



NOTES:


- 1. SUBSTRATE: FUSED SILICA
- 2. BEAM MODE: SM OR MM
- 3. SAMPLED ENERGY: 79
- 4. SAMPLED ANGLE: 0.12
- 5. COATING:
LASER V-COAT (1064nm)
- 6. BEAM SPECIFICATION:
MINIMUM BEAM DIAMETER: 3.12mm



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



| | | | | | | | |
|--------------------|----------------------|----------------------|---|----|--------|--|-----------------|
| | S1 | S2 | <div>THIRD ANGLE PROJECTION</div>  | | TITLE | 1064nm, 20mm Dia., 1x2 SPOT ARRAY, DIFFRACTIVE BEAMSPLITTER | |
| SHAPE | PLANO | PLANO | | | | | |
| MIN CLEAR APERTURE | Ø18.0 | Ø18.0 | | | | | |
| BEVEL MAX FACE | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED | ALL DIMS IN | mm | DWG NO | 14695 | SHEET 1 OF 1 |