

NOTES:

- SUBSTRATE: VACUUM UV GRADE CaF2
- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO <1 arcmin
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(AVG) ≤ 1.5% FROM 250-700nm @ 0° AOI R(ABS) ≤ 1.0% FROM 350-450nm @ 0° AOI







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2]			Edmund Option	\$S®
SHAPE	PLANO	PLANO		I		Ø5mm, UV - VIS, CALCIUM FLUORIDE WI	INDOW
SURFACE QUALITY	40-20	40-20	THIRD ANGLE . PROJECTION	$\oplus \lhd$	TITLE	SITIM, 0V - VIS, CALCION I LOCKIDE WI	
CLEAR APERTURE	Ø4.50	Ø4.50					CLIEFT
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	14800	SHEET 1 OF 1