




FOCAL LENGTH (EFL): $36 \pm 0,36$
 BACK FOCAL LENGTH (BFL): $34,9$

- 1 AR COATING: YAG-BBAR
 $R(ABS) < 0,25\% @ 532nm @ 0^\circ AOI$
 $R(ABS) < 0,25\% @ 1064nm @ 0^\circ AOI$
 $R(AVG) < 1,0\% FROM 500-1100nm @ 0^\circ AOI$
- 2 BLACKENED SURFACE

LEFT SURFACE		MATERIAL	RIGHT SURFACE	
R	$36,65 \pm 0,037$ CX	GLASS N-BK7 517/642	R	$36,65 \pm 0,037$ CX
Øe	11		Øe	11
3/	3 (0,5) $\lambda=632,8$ nm		3/	3 (0,5) $\lambda=632,8$ nm
4/	-		4/	1,93'
5/	40 - 20 (MIL-PRF-13830B)		5/	40 - 20 (MIL-PRF-13830B)
6/	-		6/	-

PROTECTIVE CHAMFERS AS NEEDED

ROHS:
COMPLIANT

SCALE:
NONE

$\lambda = 587,6nm$

FIRST ANGLE
PROJECTION



Edmund Optics®

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT
NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY: DO NOT MANUFACTURE
PARTS TO THIS DRAWING

INDICATIONS IN ACCORDANCE WITH ISO 10110

ALL DIMS
IN:

mm

TITLE

12mm Dia, x 36mm FL, YAG-BBAR
Coated, Inked, Double-Convex Lens

DWG NO

89243INK

SHEET SIZE
A4

SHEET
1 OF 1