

NOTES:


1. SUBSTRATE: VACUUM UV GRADE CaF2

- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO < 1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(AVG) < 1% FROM 1650-3000nm @ 0° AOI R(ABS) < 2% FROM 1650-3000nm @ 0° AOI

4. FINE GRIND SURFACE







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

CHARE	S1	S2			R	Edmund Optics®	3
SHAPE	PLANO	PLANO					
SURFACE FLATNESS	λ/2	λ/2		1		25.4mm Dia., 3mm Thick, BBAR (1650-3000nr	m)
SURFACE QUALITY	40-20	40-20	THIRD ANGLE PROJECTION		TITLE	Coated, Calcium Fluoride Window	''',
CLEAR APERTURE	Ø22.86	Ø22.86				SHE	CCT
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	15968	DF 1