




- NOTES:
- 1. SUBSTRATE MATERIAL:
B270
 - 2. SURFACE S1 TO BE PARALLEL TO SURFACE S2 TO WITHIN <3 ARCMIN
 - 3. COATING (APPLY ACROSS COATING APERTURE)



S1: Square Aluminum (AlMgF2) Apertures
R: 30±5% @ 400 - 2000nm @ 45° AOI
T: 70±5% @ 400 - 2000nm @ 45° AOI

S2: NONE
 - 4. POLKA DOT CENTER TO CENTER SPACING : 0.15mm
POLKA DOT MINIMUM APERTURE: 2mm
 - 5. ROHS : COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

		S1	S2	 Edmund Optics®		
SHAPE		PLANO	PLANO		TITLE	12.7mm SQ 50R/50T, VIS-NIR POLKA-DOT BEAMSPLITTER
SURFACE QUALITY		80-50	80-50			
CLEAR APERTURE		90%	90%			
BEVEL		PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO 15986
						SHEET 1 OF 1