




NOTES:

1. SUBSTRATE MATERIAL:
FLOAT GLASS
2. COATING (APPLW ACROSS CLEAR APERTURE):
S1: ALUMINUM
S2: NONE
3. BLAZE ANGLE: 22° 0'
NOMINAL BLAZE WAVELENGTH: 10000nm
GROOVE DENSITY: 75 GROOVES/mm
4. EDGES GROUND
5. RoHS COMPLIANT




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY



	S1	S2
SHAPE	PLANO	PLANO
CLEAR APERTURE	11.25 x 22.5	11.25 x 22.5

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

TITLE	Richardson Gratings™ 75 Grooves, 12.5 x 25mm, 10µm, Plane Ruled Reflection Grating
DWG NO	15771
SHEET	1 OF 1