


NOTES:

1. SUBSTRATE:
D-ZK3
2. NUMERICAL APERTURE: 0.15
3. COATING
S1 & S2: R(AVG) $\leq 0.5\%$ @ 350 - 700nm
4. FOCAL LENGTH TOLERANCE: $\pm 1\%$
5. TRANSMITTED WAVEFRONT ERROR (λ , RMS @ 632.8NM): < 0.076
6. DESIGN WAVELENGTH: 670nm



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL	15.04	Edmund Optics®	LightPath 354120 4.99mm Dia., 0.15 NA, BBAR (350-700nm), Molded Aspheric Lens	
SHAPE	CONVEX	PLANO	WD	13.20			
SURFACE QUALITY	40-20	40-20	THIRD ANGLE PROJECTION		TITLE		
CLEAR APERTURE	$\varnothing 4.50$	$\varnothing 4.20$	ALL DIMS IN	mm	DWG NO	16689	SHEET 1 OF 1
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					