



NOTES:


1. SUBSTRATE MATERIAL:  
Fused Silica (Corning 7980)
2. COATING (APPLY ACROSS CLEAR APERTURE)  
S1 & S2: Rabs  $\leq 0.25\%$  @ 880nm  
Ravg  $\leq 1.25\%$  @ 400 - 870nm  
Ravg  $\leq 1.25\%$  @ 890 - 1000nm
3.  ARROW POINTS TOWARDS TILTED SURFACE
4.  FINE GROUND SURFACE
5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
6. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
RADIUS	$\infty$	$\infty$
MIN CLEAR APERTURE	$\varnothing 22.50$	$\varnothing 22.50$
SURFACE QUALITY	20-10	20-10
SURFACE ACCURACY	$\lambda/10$	$\lambda/10$
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

 **Edmund Optics<sup>®</sup>**

TITLE: 25mm Dia., VIS-NIR Coated, Fused Silica Wedged Window

DWG NO: 17667

SHEET 1 OF 1