

NOTES:




1. SUBSTRATE: B270

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: NONE

S2: NONE

S3: NONE



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	S3
SHAPE	PLANO	PLANO	PARABOLIC
RADIUS	∞	∞	ASPHERIC
SURFACE QUALITY	160-50	80-50	160-50
CLEAR APERTURE	Ø 1.92	Ø 5.38	N/A
BEVEL	PROTECTIVE AS NEEDED		NONE



ALL DIMS IN

mm



Edmund Optics®

TITLE

45° 2.5mm Output Dia., Molded Compound
Parabolic Concentrator

DWG NO

17709

SHEET
1 OF 1