



NOTES:


1. SUBSTRATE: FUSED SILICA
2. BEAM MODE: SM OR MM
3. SAMPLED ENERGY: 74
4. SAMPLED ANGLE: 4.0 x 4.0
5. COATING:
LASER V-COAT (1064nm)
6. BEAM SPECIFICATION:
MINIMUM BEAM DIAMETER: 0.18mm



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO[®] Edmund Optics[®]

	S1	S2	THIRD ANGLE PROJECTION 		TITLE	1064nm, 18mm Dia., 5x5 SPOT MATRIX, DIFFRACTIVE BEAMSPLITTER	
SHAPE	PLANO	PLANO			ALL DIMS IN	mm	DWG NO
MIN CLEAR APERTURE	$\varnothing 16.2$	$\varnothing 16.2$					
BEVEL MAX FACE	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					