## NOTES:


- 1. SUBSTRATE: N-BK7
- 2. CENTERING TOLERANCE (AT 587.6nm): BEAM DEVIATION: ≤2 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE):

\$1, \$2, \$3, & \$4: R(AVG) <0.5% @ 430 - 670nm \$5: MULTILAYER DIELECTRIC TO ACHIEVE: TRANSMISSION > 65% ± 5% POLARIZATION < 6%


4. FINE GROUND SURFACE

LELEMENTS TO BE CEMENTED WITH NORLAND OPTICAL ADHESIVE NOA 61

6. MARK IDENTIFIES BEAMSPLITTED COATED RIGHT ANGLE PRISM







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2	
SHAPE	PLANO	PLANO	
SURFACE ACCURACY	λ/8	λ/8	
SURFACE QUALITY	40-20	40-20	
CLEAR APERTURE	> 90%	> 90%	
	,.		

		Edmund Optics			
THIRD ANGLE PROJECTION		TITLE	25mm VIS, 30R/70T, Non-Polarizing Cube Beamsplitter		
ALL DIMS IN	mm	DWG NO	13420	SHEET 1 OF 1	