




NOTES:

- 1. SUBSTRATE:
POLYMER FILM
- 2. POLARIZATION: > 88% EFFICIENCY
- 3. TRANSMISSION:
SINGLE: 38
PARALLEL: 32
CROSSED: 0.74
- 4. UV ABSORPTION: >88%
- 5. OPERATING TEMPERATURE: -50 TO 70 °C
- 6. WAVELENGTH RANGE: 450 - 675 nm
- 7. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | | | |
|--|----|--|--------------|
| THIRD ANGLE PROJECTION  | |  Edmund Optics® | |
| TITLE | | 2" x 2", 2 Pack, Linear Polarizing Film | |
| ALL DIMS IN | mm | DWG NO | SHEET 1 OF 1 |
| | | 19290 | |