

## NOTES:


1. SUBSTRATE: VACUUM UV GRADE CaF2

- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO <1 arcmin
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(ABS) ≤ 0.25% AT 880nm @ 0° AOI R(AVG) ≤ 1.25% FROM 400-870nm @ 0° AOI R(AVG) ≤ 1.25% FROM 890-1000nm @ 0° AOI









## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

|                 | \$1                  | \$2                  |  |  |
|-----------------|----------------------|----------------------|--|--|
| SHAPE           | PLANO                | PLANO                |  |  |
| SURFACE QUALITY | 40-20                | 40-20                |  |  |
| CLEAR APERTURE  | Ø11.25               | Ø11.25               |  |  |
| BEVEL           | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |  |  |
|                 |                      |                      |  |  |

|   |                        |        | <b>Edmund Optics</b> ® |  |               |
|---|------------------------|--------|------------------------|--|---------------|
|   | THIRD ANGLE PROJECTION | $\phi$ | TITLE                  | Ø12.5mm, VIS - NIR, CALCIUM FLUORIDE<br>WINDOW |               |
| D | ALL DIMS IN            | mm     | DWG NO                 | 14814  | SHEET<br>1 OF |