

NOTES:




1. SUBSTRATE: FUSED SILICA
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN <30 ARCSEC
3. COATING (APPLY ACROSS CLEAR APERTURE)

S1:R(AVG) ≥92% @ 190 - 250nm
 R(AVG) ≥83% @ 250 - 900nm
 S2: COMMERCIAL POLISH

4. S2 & EDGES FINE GRIND SURFACE

5. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATION APPLY ACROSS CLEAR APERTURE

6. ROHS COMPLIANT



**FOR INFORMATION ONLY:
 DO NOT MANUFACTURE
 PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	20-10	N/A
SURFACE FLATNESS	$\lambda/10$	N/A
COATING TYPE	METAL	N/A
COATING	ENHANCED ALUMINUM (190-900nm)	N/A
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED



ALL DIMS IN mm

TITLE	15mm Dia., Enhanced Deep UV (DUV) Mirror
DWG NO	18742
SHEET 1 OF 1	