

NOTES:

- 1. SUBSTRATE: VACUUM UV GRADE CaF2
- 2. SURFACE S2 TO BE PARALLEL WITH S1 TO <1 arcmin
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(ABS) ≤ 1.5% FROM 750-800nm @ 0° AOI R(ABS) ≤ 1.0% FROM 800-1550nm @ 0° AOI R(AVG) ≤ 0.7% FROM 750-1550nm @ 0° AOI





1 OF 1



FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

- 3.00±0.10

			1		
	SI	\$2			
SHAPE	PLANO	PLANO		I	
SURFACE QUALITY	40-20	40-20	THIRD ANGLE . PROJECTION	\oplus	T
CLEAR APERTURE	Ø36.00	Ø36.00			
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	D

			Edmund Optic	S®
HIRD ANGLE . ROJECTION		TITLE	Ø40mm, NIR II, CALCIUM FLUORIDE WIN	NDOW
ALL DIMS IN	mm	DWG NO	14832	SHEET 1 OF 1