

NOTES:

1. SUBSTRATE: N-SF5

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: VIS-EXT+ (350-700nm)

R(AVG) <0.5% @ 350 - 700nm @ ±30° AOI
R(ABS) <1.5% @ 350 - 700nm @ ±30° AOI



3. EDGES: FINE GROUND

4. CENTERING: <3 ARCMIN

5. ASPHERE FIGURE ERROR: 0.25µm RMS

6. ASPHERIC SURFACE DESCRIBED BY (REF. COEFFICIENT TABLE)

$$Z_{ASPH}(Y) = \frac{(\frac{1}{RADIUS})^2 * Y^2}{1 + \sqrt{1 - (1+k) * (\frac{1}{RADIUS})^2 * Y^2}} + D * Y^2 + E * Y^4 + F * Y^6 + G * Y^8 + H * Y^{10} + J * Y^{12} + L * Y^{14}$$




SECTION A-A

COEFFICIENT TABLE 6.

COEFFICIENT	S1
SEMI-DIAMETER	1.000000E+01
(1/RADIUS)	7.432181E-02
k	-9.143177E-01
D	0.000000E+00
E	1.841702E-05
F	2.043851E-08
G	-8.357415E-11
H	2.016516E-13
J	0.000000E+00
L	0.000000E+00

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	EFL @ 587.6nm	20.00	 Edmund Optics®		
SHAPE	CONVEX	PLANO	BFL @ 587.6nm	13.31			
RADIUS	13.455	INFINITY	THIRD ANGLE PROJECTION		TITLE	20mm Dia., 0.50 Numerical Aperture, 350-700nm Coated, Inked, High Precision Aspheric Lens	
SURFACE QUALITY	40-20	40-20					
CLEAR APERTURE	Ø18.00	Ø18.00	ALL DIMS INmm		DWG NO	16955INK	SHEET 1 OF 1
BEVEL MAX	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					