



NOTES:

1. SUBSTRATE:  
VACUUM UV GRADE CaF<sub>2</sub>
2. SURFACE S2 TO BE PARALLEL WITH S1 TO <1 arcmin
3. COATING (APPLY ACROSS CLEAR APERTURE)  
S1 & S2: R(AVG) < 1% FROM 1650-3000nm @ 0° AOI  
R(ABS) < 2% FROM 1650-3000nm @ 0° AOI


△ 4. FINE GRIND SURFACE



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE	Ø13.50	Ø13.50
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

**EO**® **Edmund Optics**®

TITLE	Ø15mm, BBAR (1650-3000nm), CALCIUM FLUORIDE WINDOW	
DWG NO	15965	SHEET 1 OF 1