NOTES:

1. SUBSTRATE:

SAPPHIRE (AL2O3)


2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN ≤3.5 ARCMIN

3. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: UNCOATED

4. FINE GRIND SURFACE

5. ROHS COMPLIANT



REV. A	S1	S2		ſ		®	
SHAPE	PLANO	PLANO				Edmund Optic	C ®
SURFACE FLATNESS	2λ (typical)	2λ (typical)					5
SURFACE ROUGHNESS	≤0.1µm PER INCH	≤0.1µm PER INCH		1		25.4mm Diameter, 6.35mm Through H	
SURFACE QUALITY	80-50	80-50	THIRD ANGLE		TITLE	Sapphire Window	1010,
	0.008	0.008		1			CULLET
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED	ALL DIMS IN	mm	DWG NO	17214	Sheet 1 OF 1