


NOTES:


1. SUBSTRATE: POLYMER FILM XP44-40
2. OPERATING TEMPERATURE: -40 TO +80 °C
3. WAVELENGTH RANGE: 400 - 700 nm
4. EXTINCTION RATIO: 2000:1
5. POLARIZATION EFFICIENCY (%): >99.95
6. TRANSMISSION (%):
SINGLE: 44.2 ±1.5
PARALLEL: 38.6
CROSSED: <0.02
7. ROHS COMPLIANT
8. THE POLARISATION AXIS IS PARALLEL TO THE NOTCH
ON THE POLARISER



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO[®] Edmund Optics[®]

THIRD ANGLE PROJECTION 		TITLE	50mm Dia. High Transmission Linear Polarizing Film (XP44-40)	
ALL DIMS IN	mm	DWG NO	19025	SHEET 1 OF 1